# CASELLA



## VAPex Personal Air Sampling Pump for Low Flow Applications



The VAPex range has been designed particularly for low flow sampling of vapours and gases in working environments. Its Instrinsically Safe design and remote operation via the Airwave App makes it ideal for modern day sampling requirements.

## www.casellasolutions.com



ASELLAS



ISI sa-nv Instrumentation for Science and Industry Rue du Doyenné 3 Dekenijstraat 1180 Brussels – Belgium - Tel 02/ 343 30 81

(INTERCONTINENTAL SERVICES INC) mail : sales@isi-be.eu web : www.isi-be.eu



#### **Key Features**

- Intrinsically Safe
- Wide low flow range 20mL 500mL/min
- Wireless Bluetooth connectivity
- Remote Start/Stop from Airwave App
- IECEx and ATEX certified EX ia IIC T4 Ga
- Pocket size form factor
- Remote calibration
- Motion sensing technology
- Auto restart function
- Simple and smooth (Noise Free) operation
- Rapid charging of battery
- Add sampling notes on the go

#### **Simple Operation**

Casella products are known in the industry for their ease of use and the VAPex is no exception to this. Using only four buttons you can easily navigate through the colour coded setup menus.

- Just tap a key to start a run
- Displays battery life in remaining hours as well as flow rate
- Intuitive colour display to show device status
- Status LEDs showing pump state from a distance



Easy to use menu



Colour coded display showing remaining battery life

## Use Airwave on your mobile device to remotely monitor multiple pumps, without disturbing the wearer!







ISI sa-nv Instrumentation for Science and Industry Rue du Doyenné 3 Dekenijstraat 1180 Brussels – Belgium - Tel 02/ 343 30 81



#### **Designed for Supreme Performance**

VAPex pumps have been designed to give optimum performance for low flow rate applications. Its highly sophisticated control mechanism allows users to collect samples at extremely low flow rates to capture vapours and gases via sorbent tubes.

- Run time of 34 hours at optimum use
- Flexibility to work with all tubes and kits
- Outstanding back pressure capability
- Excellent flow control and stability

VAPex has an outstanding back pressure capability to ensure uninterrupted smooth operation of the pump even in the most demanding settings. Innovative technology embedded in VAPex provides unique features to the user.

## "We wanted to have a dedicated low flow pump for gases, one we could use without any low flow adaptor"

#### Intelligent and Easy to Wear Design

VAPex has one of the most practical, slim and lightweight cases designed with user convenience in mind. The wearing clip comes with a lifetime guarantee.

- Display with highly visible colour coded menus
- Motion sensor to ensure compliance and operation
- Ergonomically designed case weighing only 220 grams
- Recessed inlet spigot to prevent damage
- Large buttons with lockable keypad

Screen on top to prevent damage when in use

### Bluetooth Connectivity

Monitor your VAPex remotely with Bluetooth<sup>®</sup> and the supporting Airwave App on your phone or tablet.


- Monitor the pump without disturbing the wearer
- Monitor multiple pumps
- Start and stop pumps remotely
- Email data direct to your PC

#### **Intrinsically Safe**

VAPex is an Intrinsically Safe (IECEx) pump for use in potentially hazardous atmospheres. Although VAPex is ideal for use in oil and gas, pharmaceutical and chemical industries. Its applications are also frequent where occupational health and safety is in question.

Ex ia IIC T4 Ga (Ta = -20°C to +45°C)

#### **Data Storage and Analysis**



The VAPex can store up to 200 separate runs, storing data including start time, stop time, date, duration, volume sampled and motion index.

- Simple to use download utility for PCs
- Graphs flow, motion and back pressure
- Shows events such as blockages
- Downloads into Excel to easily view and share data




ISI sa-nv Instrumentation for Science and Industry Rue du Doyenné 3 Dekenijstraat 1180 Brussels – Belgium - Tel 02/ 343 30 81

#### Technical Specification Flow Performance

Flow Range ml/min: Flow Control: Back Pressure: Run Time: 20-500 < ± 5% at setpoint 70cm @ 500mL/min 34 hours at 200mL/min (20cm H<sub>2</sub>O Back Pressure)

#### **Back Pressure vs Battery Life**



46 (LWD) mm

#### Physical

Dimensions:	86 x 82 x
Weight:	220g
IP Rating:	IP65

#### Environmental

Temperature:5°C - 45°CBarometric Pressure:Auto-correcting

#### Electrical

Battery Type:High capacity Li-ion batteryChargers:Single or 5-way dock, <6hrs charge time</td>

#### **Model Selection**

VAPex	Standard	Pro
Intrinsically Safe	•	•
Motion Sensor	•	٠
Constant Pressure Mode		•
Bluetooth		٠
PC Download		٠
Run Duration Timer		•
Fully Programmable Timers		•
Logging of Flow and Motion		

#### **Ordering Information**

VAPEX	VAPex I.S Standard Pump
VAPEXPRO	VAPex I.S Pro Pump

All pumps include 1m tube, Field Guide and a Certificate of Calibration and Conformity.

214020B/KIT	Single Docking Station for VAPex inc PSU & USB Cable
214024C/KIT	5-Way Docking Station for VAPex inc PSU & USB Cable
VAPEX/KIT	5-Way VAPex Standard Kit with tubing, docking station, PSU with universal connections and USB cable
VAPEXPRO/KIT	5-Way VAPex Pro Kit with tubing, docking station, PSU with universal connections and USB cable

VAPex pump with 5-way charger



#### **Related Products**

Connect the VAPex with our Flow Detective to run seamless calibration through your Airwave App.



SM134 V1



ISI sa-nv Instrumentation for Science and Industry Rue du Doyenné 3 Dekenijstraat 1180 Brussels – Belgium - Tel 02/ 343 30 81

(INTERCONTINENTAL SERVICES INC) mail : sales@isi-be.eu web : www.isi-be.eu